

☐ **G1753** Eye/Face Wash, Wall Mounted, Stainless Steel Bowl and Skirt



Application: Eye/face wash for wall mounting. Unit has stainless steel bowl and wrap-around skirt to conceal valve, drain and piping. Ideal for laboratories and other areas where clean, uncluttered appearance is desired.

Spray Head Assembly: Two FS-Plus[™] spray heads. Each head has a "flip top" dust cover, internal flow control and filter to remove impurities from the water flow.

Valve: 1/2" IPS brass stay-open ball valve. Valve is US-made with chrome plated brass ball and PTFE seals.

Bowl: 11-1/2" diameter stainless steel with wraparound skirt.

Mounting: Welded stainless steel wall bracket.

Supply: 1/2" NPT female inlet. Waste: 1-1/4" NPT female outlet.

Sign: ANSI-compliant identification sign.

Quality Assurance: Unit is completely assembled and water


tested prior to shipment.

Available Options

- HS Auxiliary hand-held drench hose for rinsing eyes, face or body.
- T Chrome plated brass tailpiece and trap with 1-1/2" IPS waste connection.
- TP 1-1/2" OD chrome plated brass tailpiece.
- G3600LF Thermostatic mixing valve precisely blends hot and cold water to deliver warm (tepid) water as required by ANSI Z358.1-2014. Refer to "Tempering Valves" section for complete technical and product selection information.



☐ **G1753** Eye/Face Wash, Wall Mounted, Stainless Steel Bowl and Skirt



- EACH FS-PLUS™ SPRAY HEAD HAS A
 "FLIP-TOP" DUST COVER, INTERNAL FLOW
 CONTROL AND FILTER TO REMOVE IMPURITIES
 FROM THE WATER FLOW.
- 2. UNIT SHOULD BE INSTALLED SUCH THAT WATER FLOW PATTERN IS POSITIONED BETWEEN 33" AND 53" ABOVE FLOOR.

THIS SPACE FOR ARCHITECT/ENGINEER APPROVAL

Due to continuing product improvement, the information contained in this document is subject to change without notice. All dimensions are \pm 1/4" (6mm). rev. 081018

Sign Included



